



General		
Shape	Square	
Seating Capacity	6	
Shell Material	Ultralife™ / Granitex™ / Geloy®	
Dimensions	91 ½" x 91 ½" x 35" H / (232cm X 232 cm x 90 cm H)	
Corner Radii	16 in. (41 cm)	
Water Capacity	400 Gallons (1514 Liters)	
Dry Weight	920 lbs (418 kg)	
Shipping Weight	Domestic 920 lbs (418 kg) - Export 970 lbs (440 kg)	
Full Weight	4260 lbs (1933 kg)	
Skirt Material	Domestic Synthetic - Export Wood or Synthetic	
Poly Floor	Yes	
Water System		
Water Treatment System	Ultra Pure™	
Plumbing Systems	4	
Filters/Coverage	2 / 75 sq. ft.	
Gate Valves	4	
VCR Jet® - Air Adjustable/Directional	8	
VCR Jet® - Rotator	12	
VCR Jet® - Dual Rotator	0	
VCR Jet® - Multi Port Spinner	0	
VCR Jet® - Mini Rotator	10	
VCR Jet® - Mini Directional	6	
VCR Jet® - Euro Directional	0	
VCR Jet® - Euro Rotator	0	
VCR Jet® - Mini Directional in NFJ	12	
Typhoon Jet	1	
Ozone Jet	1	
Heater Return Jet	1	
Pump Returns	4	
Diverter Valves	2	
Floor Drains	1	
Skimmer	8" Weir	
Special Features		
Dynamic Massage Sequencer w/ control panel	Yes	
NeckFlex® Jet Pillows	3	
Headrest Pillows	0	
Stereo system	Optional Advanced In.Tune	
Water Feature	Optional with LFX package	
Water Feature Volume control	Optional with LFX package	
Cup Holders	3	
Tactile Therapy	Foot & hand	
Pump Information		
	Domestic (60Hz)	Export (50Hz)
Motor Size – Peak (Continuous) HP	4.0 (2.5) Hp	3.6 (2.0) HP
Jet Pumps # of Pumps/Speed	Two / Dual	Two / single
Circulation pump	1	1
Fountain pump	n/a	n/a
Electrical System		
	Domestic (60Hz)	Export (50Hz)
Voltage	240	240
Amperage	50/40/30	1X16 / 2X16 / 1X32
Heater	FastFlo 2.7,4.0,5.5 kW	FastFlo 2.9 kW
Thermostat	Electronic	Electronic
Light	1 with optional LED	Multi color LED
Control System	MSPA-MP-D17-NON LFX, MSPA-MP-D18 LFX	MSPA-MP-CE-D17-N/LFX, D18 LFX
Upper Control (programmable)	M-DRIVE with Scrolling Message Center	M-DRIVE with Scrolling Message Center
Auxiliary Upper Control	Yes	Yes



Note: 1. Subject to change without notice.

Chairman II Architectural Specification



Note: 1. Subject to change without notice.

2. Engineering specs may differ slightly from brochure.
3. For E-Z lifter installation allow 18" clearances on the backside of the spa.
4. Alternative cabinets may add significant weight. Ask your dealer for exact details
5. This is the approximate location for drilling a hole if you must bring the power line in through the bottom of the spa. Be careful not to puncture a plumbing line inside the equipment compartment(drill from the inside compartment out).

Dimensions shown as inches and [centimeters] - XX" [cm]

Caution:
Due to manufacturing tolerances there could be some minor differences between the actual spa and the drawing above. If site planning is critical to such tolerances, be sure to measure your actual spa.